




CORTE AA



CORTE BB



EXEMPLOS DE MANUSEIO DA TABELA DE PVs TIPO			
EX. 01 - GALERIA EM TANGENTE	EX. 02 - GALERIA EM TANGENTE	PV TIPO 3 NORMAL	PV TIPO 4 NORMAL
EX. 03 - GALERIA EM CURVA	EX. 04 - GALERIA EM CURVA	PV TIPO 5 ESCONSO	PV TIPO 1 NORMAL

DETALHAMENTO DAS VIGAS

CORTE

VIGAS V1/V2/V3/V4/V5

L1 (230 x 230 x 12)

L2 (150 x 230 x 12)

L3 (150 x 230 x 12)

L4 (150 x 230 x 12)

L5 (150 x 230 x 12)

L6 (150 x 230 x 12)

L7 (150 x 230 x 12)

L8 (150 x 230 x 12)

L9 (150 x 230 x 12)

L10 (150 x 230 x 12)

L11 (150 x 230 x 12)

L12 (150 x 230 x 12)

L13 (150 x 230 x 12)

L14 (150 x 230 x 12)

L15 (150 x 230 x 12)

L16 (150 x 230 x 12)

L17 (150 x 230 x 12)

L18 (150 x 230 x 12)

L19 (150 x 230 x 12)

L20 (150 x 230 x 12)

L21 (150 x 230 x 12)

L22 (150 x 230 x 12)

L23 (150 x 230 x 12)

L24 (150 x 230 x 12)

L25 (150 x 230 x 12)

L26 (150 x 230 x 12)

L27 (150 x 230 x 12)

L28 (150 x 230 x 12)

L29 (150 x 230 x 12)

L30 (150 x 230 x 12)

L31 (150 x 230 x 12)

L32 (150 x 230 x 12)

L33 (150 x 230 x 12)

L34 (150 x 230 x 12)

L35 (150 x 230 x 12)

L36 (150 x 230 x 12)

L37 (150 x 230 x 12)

L38 (150 x 230 x 12)

L39 (150 x 230 x 12)

L40 (150 x 230 x 12)

L41 (150 x 230 x 12)

L42 (150 x 230 x 12)

L43 (150 x 230 x 12)

L44 (150 x 230 x 12)

L45 (150 x 230 x 12)

L46 (150 x 230 x 12)

L47 (150 x 230 x 12)

L48 (150 x 230 x 12)

L49 (150 x 230 x 12)

L50 (150 x 230 x 12)

L51 (150 x 230 x 12)

L52 (150 x 230 x 12)

L53 (150 x 230 x 12)

L54 (150 x 230 x 12)

L55 (150 x 230 x 12)

L56 (150 x 230 x 12)

L57 (150 x 230 x 12)

L58 (150 x 230 x 12)

L59 (150 x 230 x 12)

L60 (150 x 230 x 12)

L61 (150 x 230 x 12)

L62 (150 x 230 x 12)

L63 (150 x 230 x 12)

L64 (150 x 230 x 12)

L65 (150 x 230 x 12)

L66 (150 x 230 x 12)

L67 (150 x 230 x 12)

L68 (150 x 230 x 12)

L69 (150 x 230 x 12)

L70 (150 x 230 x 12)

L71 (150 x 230 x 12)

L72 (150 x 230 x 12)

L73 (150 x 230 x 12)

L74 (150 x 230 x 12)

L75 (150 x 230 x 12)

L76 (150 x 230 x 12)

L77 (150 x 230 x 12)

L78 (150 x 230 x 12)

L79 (150 x 230 x 12)

L80 (150 x 230 x 12)

L81 (150 x 230 x 12)

L82 (150 x 230 x 12)

L83 (150 x 230 x 12)

L84 (150 x 230 x 12)

L85 (150 x 230 x 12)

L86 (150 x 230 x 12)

L87 (150 x 230 x 12)

L88 (150 x 230 x 12)

L89 (150 x 230 x 12)

L90 (150 x 230 x 12)

L91 (150 x 230 x 12)

L92 (150 x 230 x 12)

L93 (150 x 230 x 12)

L94 (150 x 230 x 12)

L95 (150 x 230 x 12)

L96 (150 x 230 x 12)

L97 (150 x 230 x 12)

L98 (150 x 230 x 12)

L99 (150 x 230 x 12)

L100 (150 x 230 x 12)

L101 (150 x 230 x 12)

L102 (150 x 230 x 12)

L103 (150 x 230 x 12)

L104 (150 x 230 x 12)

L105 (150 x 230 x 12)

L106 (150 x 230 x 12)

L107 (150 x 230 x 12)

L108 (150 x 230 x 12)

L109 (150 x 230 x 12)

L110 (150 x 230 x 12)

L111 (150 x 230 x 12)

L112 (150 x 230 x 12)

L113 (150 x 230 x 12)

L114 (150 x 230 x 12)

L115 (150 x 230 x 12)

L116 (150 x 230 x 12)

L117 (150 x 230 x 12)

L118 (150 x 230 x 12)

L119 (150 x 230 x 12)

L120 (150 x 230 x 12)

L121 (150 x 230 x 12)

L122 (150 x 230 x 12)

L123 (150 x 230 x 12)

L124 (150 x 230 x 12)

L125 (150 x 230 x 12)

L126 (150 x 230 x 12)

L127 (150 x 230 x 12)

L128 (150 x 230 x 12)

L129 (150 x 230 x 12)

L130 (150 x 230 x 12)

L131 (150 x 230 x 12)

L132 (150 x 230 x 12)

L133 (150 x 230 x 12)

L134 (150 x 230 x 12)

L135 (150 x 230 x 12)

L136 (150 x 230 x 12)

L137 (150 x 230 x 12)

L138 (150 x 230 x 12)

L139 (150 x 230 x 12)

L140 (150 x 230 x 12)

L141 (150 x 230 x 12)

L142 (150 x 230 x 12)

L143 (150 x 230 x 12)

L144 (150 x 230 x 12)

L145 (150 x 230 x 12)

L146 (150 x 230 x 12)

L147 (150 x 230 x 12)

L148 (150 x 230 x 12)

L149 (150 x 230 x 12)

L150 (150 x 230 x 12)

L151 (150 x 230 x 12)

L152 (150 x 230 x 12)

L153 (150 x 230 x 12)

L154 (150 x 230 x 12)

L155 (150 x 230 x 12)

L156 (150 x 230 x 12)

L157 (150 x 230 x 12)

L158 (150 x 230 x 12)

L159 (150 x 230 x 12)

L160 (150 x 230 x 12)

L161 (150 x 230 x 12)

L162 (150 x 230 x 12)

L163 (150 x 230 x 12)

L164 (150 x 230 x 12)

L165 (150 x 230 x 12)

L166 (150 x 230 x 12)

L167 (150 x 230 x 12)

L168 (150 x 230 x 12)

L169 (150 x 230 x 12)

L170 (150 x 230 x 12)

L171 (150 x 230 x 12)

L172 (150 x 230 x 12)

L173 (150 x 230 x 12)

L174 (150 x 230 x 12)

L175 (150 x 230 x 12)

L176 (150 x 230 x 12)

L177 (150 x 230 x 12)

L178 (150 x 230 x 12)

L179 (150 x 230 x 12)

L180 (150 x 230 x 12)

L181 (150 x 230 x 12)

L182 (150 x 230 x 12)

L183 (150 x 230 x 12)

L184 (150 x 230 x 12)

L185 (150 x 230 x 12)

L186 (150 x 230 x 12)

L187 (150 x 230 x 12)

L188 (150 x 230 x 12)

L189 (150 x 230 x 12)

L190 (150 x 230 x 12)

L191 (150 x 230 x 12)

L192 (150 x 230 x 12)

L193 (150 x 230 x 12)

L194 (150 x 230 x 12)

L195 (150 x 230 x 12)

L196 (150 x 230 x 12)

L197 (150 x 230 x 12)

L198 (150 x 230 x 12)

L199 (150 x 230 x 12)

L200 (150 x 230 x 12)

L201 (150 x 230 x 12)

L202 (150 x 230 x 12)

L203 (150 x 230 x 12)

L204 (150 x 230 x 12)

L205 (150 x 230 x 12)

L206 (150 x 230 x 12)

L207 (150 x 230 x 12)

L208 (150 x 230 x 12)

L209 (150 x 230 x 12)

L210 (150 x 230 x 12)

L211 (150 x 230 x 12)

L212 (150 x 230 x 12)

L213 (150 x 230 x 12)

L214 (150 x 230 x 12)

L215 (150 x 230 x 12)

L216 (150 x 230 x 12)

L217 (150 x 230 x 12)

L218 (150 x 230 x 12)

L219 (150 x 230 x 12)

L220 (150 x 230 x 12)

L221 (150 x 230 x 12)

L222 (150 x 230 x 12)

L223 (150 x 230 x 12)

L224 (150 x 230 x 12)

L225 (150 x 230 x 12)

L226 (150 x 230 x 12)

L227 (150 x 230 x 12)

L228 (150 x 230 x 12)

L229 (150 x 230 x 12)

L230 (150 x 230 x 12)

L231 (150 x 230 x 12)

L232 (150 x 230 x 12)

L233 (150 x 230 x 12)

L234 (150 x 230 x 12)

L235 (150 x 230 x 12)

L236 (150 x 230 x 12)